

# Cross Reference Chart



Pipe-Lock Joint Restraint Couplings						
Description	Smith-Blair	EBAA	Ford	Romac	JCM	PowerSeal
Join Ductile Iron X Ductile Iron Pipe	471	(3800)	(RCDD)	440RG	-	-
Join PVC X PVC Pipe	472	(3800)	(RCPP)	440RG	-	-
Join PVC X Ductile Iron/Carbon Steel Pipe	473	(3800)	(RCDP)	440RG	-	-
Join Ductile Iron X Ductile Iron Pipe - Reducing	474	-	-	-	-	-
Join PVC X PVC Pipe - Reducing	475	-	-	-	-	-
Join PVC X Ductile Iron Pipe - Reducing	476	-	-	-	-	-
Sleeve Only	477	-	-	-	-	-
Flange-Lock Joint Restraint FCA						
Description	Smith-Blair	EBAA	Ford	Romac	JCM	PowerSeal
Join Ductile Iron Pipe to Flanged Fittings	911	(2100)	(RFAD)	(RFCA)	(SFA)	(3200)
Join PVC Pipe to Flanged Fittings	920	(2100)	(RFAP)	PVC RFCA	(SFA)	(4200)
Sleeve Only	923	-	-	-	-	-
Restraint Couplings						
Description	Smith-Blair	Dresser	Ford	Romac	JCM	PowerSeal
EZ-W Steel Couplings, Straight	EZWS	(711)	-	-	-	-
EZ-W Steel Couplings, Reducing	EZWR	(711)	-	-	-	-
EZ-W Steel Flange Coupling Adapter	EZWF	-	-	-	-	-
EZ-W Steel Pipe End Cap	EZWC	-	-	-	-	-
Steel Couplings w/Anchor Studs	414	-	-	-	-	-
Full Circle Repair Clamps						
Description	Smith-Blair	Dresser	Ford	Romac	JCM	PowerSeal
Single Band-Cast Lugs, Low Pressure	221	-	-	(LSS1)	(108)	-
Single Band-Cast Lugs	226	360	F1	CL1	(101), 171	3121
Double Band-Cast Lugs	227	361	F2	CL2	(102), 172	3122
Multi-Band-Cast Lugs	228	360	F3	CL3	(102), 172	3123
Collar Leak Clamp-Cast Lugs	229	-	FCC	-	(105), 175	3141
Tapped, Single Band-Cast Lugs	238	SPEC360	F1	IP/CC	(103), 173	3131
Tapped, Double Band-Cast Lugs	239	SPC361	F2	IP/CC	(104), 174	3132
Full Circle Redi-Clamp-Cast Lugs	244	-	FSC	SCC	111	3153PS
Full Circle Redi-Clamp, All Stainless	247	-	FLSC	(SCS)	111AS	-
Single Band-Cast Lugs, All Stainless	256	[364]	FSL1	(CL1)	(131)	3121CS
Double Band-Cast Lugs, All Stainless	257	360	FSL2	(CL2)	(132)	-
Single Band-Fab Lugs, All Stainless	261	364	FS1	SS1	161	3121AS
Double Band-Fab Lugs, All Stainless	262	364	FS2	SS2	162	3122AS
Multi-Band-Fab Lugs, All Stainless	263	364	FS3	SS3	162	3123AS
Tapped, Single Band-Fab Lugs, All Stainless	264	-	FS1	IP/CC	163	3131AS
Tapped, Double Band-Fab Lugs, All Stainless	265	-	FS2	IP/CC	164	3132AS
Higher Pressure, Carbon Steel, V Lugs	267-000	-	-	-	-	-
Higher Pressure, SS, V Lugs	267-065	-	-	-	136	3122AS HP
Higher Pressure, SS, Fab Lugs	268	-	-	-	-	-
Collar Leak Clamp-Fab Lugs, All Stainless	269	-	FCC	CLC	(135)	3143AS
Patch Clamps						
Description	Smith-Blair	Dresser	Ford	Romac	JCM	PowerSeal
Redi-Clamp-Cast Lugs	245	118	FSC	SC	110	3151
Redi-Clamp, All Stainless	248	-	FLSC	(C)	110AS	(3151AS)
Pipe Repair Clamp, Double Band-Cast Lugs	246	77, 79	-	(CC)	113	3151 HD
Bell Joint Leak Clamp						
Description	Smith-Blair	Dresser	Ford	Romac	JCM	PowerSeal
Bell Joint Leak Clamp	274	60, 160	FBC	516/416/418	142, 143	32, 313, 232

Service Saddles						
Description	Smith-Blair	Dresser	Ford	Romac	JCM	PowerSeal
Single Carbon Steel Bale - Iron Body	311	291	F101	(101U), 101NU	(401), 407	3411DI
Double Carbon Steel Bale - Iron Body	313	291	F202	(202U), 202NU	(402), 408	3413
Single Stainless Steel Strap - Iron Body	315	-	FC101, FS101	(101S), 101NU	(403), 405	3415
Double Stainless Steel Straps - Iron Body	317	-	FCD202	(202S), 202NS	(404), 406	3417DI
Wide Stainless Steel Strap - Bronze Body	325-000	-	202BS	-	-	(3409), (3407)
Double Stainless Steel Straps - Bronze Body	325-100	-	202BSD	202BS	-	3409
Repair, Double Carbon Steel Bale - Iron Body	331	-	FR202	-	-	-
Double Stainless Steel Straps, Large Tap - Iron Body (O.D specific for PVC and Steel Pipe)	357	-	(FS202), (F202)	-	-	-
Double Carbon Steel Bale - Iron Body (For Concrete Cylinder Pipe)	362	-	-	-	425	-
Triple Carbon Steel Bale - Iron Body (For Large Diameter Pipe)	366	-	-	-	-418	-
Single Stainless Steel Stud - All Stainless	371	-	FS303, FS313	304	-	3411AS
Double Stainless Steel Stud - All Stainless	372	-	FS303, FS313	306	502	3412AS
Wide Stainless Steel Strap - Iron Body (O.D. Specific for PVC or Ductile Iron)	397	0	FC202	-	-	3417SW
Couplings & End Caps						
Description	Smith-Blair	Dresser	Ford	Romac	JCM	PowerSeal
Steel Couplings	411 Reg.	38, STAB 38	FC3, FC4	400/511	201, 211	3538
Steel Couplings	411 Long	40, STAB 40	FLC	400	202	3540
Steel Couplings, Transition	413	162, 62TY.1	FC23, FC24, FC5	TC400	203	-
Steel Couplings, Reducing	415	62TY.2	FC6	RC400	204	3562R
Steel Couplings, Insulating	416	39	+FIB	IC400, IC501	-	3539
Steel Couplings, Transition Insulating	417	-	+FIB	-	-	-
Steel Couplings, Tee w/Outlet	418	-	-	-	-	-
Steel Couplings, Wide Range Two Bolt, Standard Sleeve	421	TX3	Bowling	Macro	-	-
Steel Couplings, Wide Range Two Bolt, Long Sleeve	422	-	-	-	-	-
Cast Omni Couplings System, Standard Sleeve	441	253	FC1, FC2A	501	210, 211, 212	3501
Cast Omni Couplings System, Long Sleeve	442	253	C1-L12, FC2A-L12	501	215	3501LB
Cast Omni Reducing Couplings	R441	253	FRC	FC501	-	3506R
Cast Quantum Coupling, Wide Range, Standard Sleeve	461	-	FC2W	XR501	241	3506, (3506AS)
Cast Quantum Coupling, Wide Range, Long Sleeve	462	-	FC2W-L12	XR501	242	-
Pipe End Caps, Steel	481	31	FC4	EC400	-	3551
Pipe End Caps, Cast	482	231	FEC	EC501	214	3501EC, (3506EC)
Compression Couplings	525	65 Long	C Series	702	220	3504

<b>Expansion Joints</b>						
<b>Description</b>	<b>Smith-Blair</b>	<b>Dresser</b>	<b>Ford</b>	<b>Romac</b>	<b>JCM</b>	<b>PowerSeal</b>
<b>Plain Single End</b>						
without Limit Rods	611	63TY-1	FEJ 1	EJ401	801	3563-SE
with Limit Rods	611	63TY-3	FEJ 1	EJ403	801	3563-SELR
<b>Plain Double End</b>						
without Limit Rods	612	63TY-2	FEJ 2	EJ402	802	3563-DE
with Limit Rods	612	63TY-4	FEJ 2	EJ404	802	3563-DELRL
<b>Tapping Sleeves</b>						
<b>Description</b>	<b>Smith-Blair</b>	<b>Dresser</b>	<b>Ford</b>	<b>Romac</b>	<b>JCM</b>	<b>PowerSeal</b>
Steel	622	610	FTS, FTSC	FTS420	412	3460
Steel Split Coupling Type	623	-	-	FTS425	(414)	-
Steel Split MJ Type	624	-	-	(FTS425)	414	-
Steel For Concrete Cylinder Pipe	625	-	-	FTS435	415	3431
Steel Weld-On, Top Only	626	-	FWS	FTS445	416	3428
Steel Weld-On, Full Body	627	-	-	FTS445	417	3428
Stainless Steel Body, Fab Lugs, with Carbon Steel Coated Flange	662	630	FAST	SST	-	3480
All Stainless Steel, Fab Lugs	663	630	FAST	SST	-	3480
Stainless Steel Body, V Lugs, with Carbon Steel Coated Flange	664	640	FTSS	SSTIII	462	3490
All Stainless Steel, V Lugs	665	640	FTSS	SSTIII	432	3490
Steel Plug Line Stop (662 Style)	682	-	-	-	-	-
Steel Plug Line Stop (663 Style)	683	-	-	SST-X	-	-
Steel Plug Line Stop (664 Style)	684	-	-	-	440 T4	-
Steel Plug Line Stop (665 Style)	685	-	-	-	440 T1	-
Steel Plug or Pin Line Stop (622 Style)	687	-	-	-	440 T2, 440 T12	-
Steel Pin Line Stop (625 Style)	689	-	-	-	-	-
<b>Flanged Coupling Adapters</b>						
<b>Description</b>	<b>Smith-Blair</b>	<b>Dresser</b>	<b>Ford</b>	<b>Romac</b>	<b>JCM</b>	<b>PowerSeal</b>
Cast	912	127	FFCA	FCA501	301	3521
Steel	913	128	FCA	FC400	303	3528
Steel Reducing	914	-	-	FC400	304/306	-
Steel Wide Range Single Bolt	921	-	-	-	-	-
Flanged Meter Adapters	926	131	-	-	-	-
Cast Insulated	932	-	FFCA+FIB	-	-	-
Steel Insulated	933	-	FCA+FIB	-	-	-
<b>Dismantling Joints</b>						
<b>Description</b>	<b>Smith-Blair</b>	<b>Dresser</b>	<b>Ford</b>	<b>Romac</b>	<b>JCM</b>	<b>PowerSeal</b>
Dismantling Joint	971	131	FDJ	(DJ400)	309	3563
Dismantling Joint, Full Rod Restraining	972	-	-	-	-	-
Dismantling Joint, Cam-Lock Restraining	973	-	-	(DJ405)	-	-
Dismantling Joint, Rod Restraining	975	-	FDJ-R	(DJ400)	-	3563
<b>Miscellaneous Products</b>						
<b>Description</b>	<b>Smith-Blair</b>	<b>Dresser</b>	<b>Ford</b>	<b>Romac</b>	<b>JCM</b>	<b>PowerSeal</b>
Fabricated Restraint Plates for Flanges	907	-	-	490	-	-

**NOTES:**

1. "( )" = Similar Product

2. "-" = Equivalent Product Not Available or Unknown

3. Data compiled from public information and is to be used for reference only. Product and material specifications should be confirmed prior to specification or purchase.