
Installation instructions


Exchange electrode

AmmoLyt® NHA/AT

for the AmmoLyt® NHA reference electrode




Insert the AmmoLyt® NHA/AT exchange electrode in the AmmoLyt® NHA reference electrode:



1	Remove the watering cap (1) and nut (2) from the exchange electrode. Store both accessories. You need them if you want to store the reference electrode.

2 Screw the AmmoLyt® NHA/AT exchange electrode into the AmmoLyt® NHA reference electrode without leaving any gap. A flat wrench (wrench size 13 mm) or the protective hood of the sensor is suitable as a wrench (see following figure).



Caution

The membrane and junction of the electrode must never

- **dry up (observe notes on storage)**
- **be damaged**
- **be brought into contact with grease.**

Note

After installing the electrode tap your finger against the combination electrode to remove any air bubbles from the back of the membrane. When doing so hold the electrode in an upright position (membrane downward).

Cleaning

In built-in condition:
Splash the AmmoLyt® NHA/AT electrode with water. Remove coarse contamination using a soft toothbrush under running water.

Note

For the Technical Data of the electrode, refer to the operating manual of the AmmoLyt® NHA reference electrode.

Instructions on how to install the electrode in the AmmoLyt® 700 IQ sensor are given in the operating manual of the AmmoLyt® 700 IQ sensor.