

This list is an overview of the "Build America, Buy America Act" compliance status for Xylem's Smith-Blair standard product offering. If a product you need is not listed, please contact Smith-Blair Customer Service to see if a special fabrication is available, that is BABA compliant for your project.

Locate the model number in the first column. Current BABA status is in column three.

### If column 3 "BABA Status" has

"Y" (Yes) the current product is BABA compliant but may require a "special designator" (Column 5) added to the end of the part number to ensure all domestic parts are used. **Example: Standard product 261-00069012-000 (may use import component), 261-00069012-000B is BABA compliant**

"N" (No) see the alternate product Smith-Blair offers in column 6. This alternate will work in the application but may utilize different material construction and may need a special designator.

Model Number	Product Description	BABA Status	Sizes Available	Special Designator (if required)	BABA Alternate Model Number	COMMENTS
<b>Repair Clamps</b>						
226	Full Circle Repair Clamps, Single Band	N			261	
227	Full Circle Repair Clamps, Double Band	N			262	
228	Full Circle Repair Clamps, Triple Band	N			263	
229	Full Circle Collar Leak Clamps, Single Band	N			269	
238	Full Circle Repair Clamps, Single Band, Tapped	N			264	
239	Full Circle Repair Clamps, Double Band, Tapped	N			265	
244	Full Circle Redi-Clamps	N				
245	Redi-Clamps, Partial Coverage	N				
246	Pipe Repair Clamps, Double Band	N				
247	Full Circle Redi-Clamps, All 304 SS	N				
248	Redi-Clamps, All 304 SS	N				

Model Number	Product Description	BABA Status	Sizes Available	Special Designator (if required)	BABA Alternate Model Number	COMMENTS
256	Full Circle Repair Clamps, Single Band, All 304 SS	N				
257	Full Circle Repair Clamps, Double Band, All 304 SS	N				
261	Full Circle Repair Clamps, Single Band, All 304 SS	Y	All sizes	B		
262	Full Circle Repair Clamps, Double Band, All 304 SS	Y	All sizes	B		
263	Full Circle Repair Clamps, Multi-Band, All 304 SS	Y	All sizes	B		
264	Tapped Full Circle Repair Clamps, Single Band, All 304 SS	Y	All sizes	B		
265	Tapped Full Circle Repair Clamps, Double Band, All 304 SS	Y	All sizes	B		
267	Full Circle Repair Clamp, Carbon Steel, Higher Pressure	Y	All sizes	B		
268	Full Circle Repair Clamp, Stainless Steel, Higher Pressure	Y	All sizes	B		
269	Full Circle Collar Leak Clamps, Single Band	Y	All sizes	B		
274	Bell Joint Leak Clamp, Alloy	Y	4"-12"	B		All other domestic sizes fabricated from steel.
281	Full Circle Wide Range Repair Clamp	N				
<b>Service Saddles</b>						
311	Service Saddles, Single Bale, Ductile Iron	N				
313	Service Saddles, Double Bale, Ductile Iron	N			383	
315	Service Saddles, Single Bale, Ductile Iron	N				
317	Service Saddles, Double Straps, Ductile Iron	Y	4"-8" 12"	B	387 sizes larger than 12"	4" - 12" limited to tap under 2"

Model Number	Product Description	BABA Status	Sizes Available	Special Designator (if required)	BABA Alternate Model Number	COMMENTS
325	Bronze Service Saddles, Extra Wide 304 SS Strap	Y	All sizes			BABA compliant AIS not applicable
331	Repair Service Saddle, Double Bale, Epoxy Coated DI Body	N				
357	Service Saddle, Stainless Steel Straps, DI Body	N				
362	Service Saddles, DI Body with Epoxy Coated Straps	N				
366	Service Saddles for Large Dia., DI Body, Epoxy Coated Straps	N				
371	Service Saddles, Single Stud, All 304 SS	Y	All sizes	B		
372	Service Saddles, Double Stud, All 304 SS	Y	All sizes	B		
377	Service Saddles, Wide Range, Double Stud, All 304 SS	N				
383	Steel Fabricated Service Saddles, Double Steel Fabricated Strap	Y	6" and larger			Fabricated steel body and straps
387	Steel Fabricated Service Saddles, Double SS Straps	Y	6" and larger	B		Fabricated steel body and stainless steel straps
397	Service Saddles for DI Sized pipe and PVC	Y	4"-8" 12"	B		
<b>Couplings</b>						
411	Steel Couplings	Y	3" and larger	B		Component material may vary by size
413	Steel Transition Couplings	Y	2" and larger	B		Component material may vary by size
415	Steel Reducing Couplings, Alloy Bolts & Nuts	Y	3" and larger	B		Component material may vary by size
416	Steel Insulating Couplings, Single Boot, Alloy Bolts & Nuts	Y	3" and larger	B		Component material may vary by size
418	Tee Couplings, Smaller Diameter Pipe	N				
421	Top Bolt Couplings	Y	2"-12"	B		No offering for BABA 10" & 12" oversized
422	Top Bolt Long Sleeve Couplings	Y	2"-12"	B		No offering for BABA 10" & 12" oversized

Model Number	Product Description	BABA Status	Sizes Available	Special Designator (if required)	BABA Alternate Model Number	COMMENTS
441	OMNI Cast Couplings, Straight & Transition	Y	2"-12" (DI to DI)	B		Some flange combinations require fabricated steel components
441	Components	Y	2"-12" (DI to DI)	B		Some combinations require fabricated steel components
442	OMNI Long Sleeve Couplings, Straight & Transition	Y	4"-12" (DI to DI)	B		All sleeves are fabricated steel; some flange combinations require fabricated steel components
442	Components	Y	4"-12" (DI to DI)	B		Some combinations require fabricated steel components
461	Quantum Couplings	N			421	
462	Quantum Couplings, 12" Sleeve	N			422	
481	Steel End Cap	Y	3" and larger	B		Component material may vary by size
482	OMNI Cast Pipe End, Alloy Bolts & Nuts	Y	2"-12" (DI only)	B	481	Some combinations require fabricated steel components
482	Components	N				
525	Compression Couplings	N				
<b>Tapping Sleeves</b>						
622	Carbon Steel Tapping Sleeve	Y		B		
623	Fabricated MJ Joint Tapping Sleeves	Y		B		
624	Fabricated MJ Joint Tapping Sleeves	Y		B		
625	Tapping Sleeves For Concrete Cylinder Pipe	Y		B		
626	Weld On Tapping Sleeves	Y		B		
627	Tapping Sleeves, Fabricated Weld On Outlet	Y		B		
662/663	Stainless Steel Tapping Sleeves with MJ Outlet	Y		B		
663WR	Wide Range All SS Tapping Sleeves (available w MJ Outlet)	Y	All sizes	B		
664/665	Stainless Steel Tapping Sleeves with MJ Outlet	Y		B		
68X	Line Stop Outlets for Tapping Sleeves	Y		B		

Model Number	Product Description	BABA Status	Sizes Available	Special Designator (if required)	BABA Alternate Model Number	COMMENTS
<b>Flanged Coupling Adapters</b>						
912	OMNI Flanged Coupling Adapters	N			913	913 fabricated steel
912	OMNI Components	N			913	913 fabricated steel
913	Flanged Coupling Adapters, Steel	Y		B		
914	Reducing Flanged Coupling Adapters	Y		B		
921	Top Bolt Flanged Coupling Adapters	Y		B		
922	Top Bolt Long Sleeve Flanged Coupling Adapters	Y		B		
926	Flexible Meter Coupling	N				
<b>Dismantling Joints</b>						
971	Non Restrained Dismantling Joints	Y		B		
972	Heavy Duty Restrained Dismantling Joints	Y		B		
973	Restrained Dismantling Joints	Y	4"-12"	B		
975	Restrained Dismantling Joints	Y		B		
<b>Expansion Joints</b>						
611	Expansion Joints, Single End 10" Expansion	Y		B		
612	Expansion Joints, Double End 10" Expansion	Y		B		
<b>Restraints</b>						
EZW	Straight Seal & Restraint Couplings	N	4"-12"		470 series w/ "B"	
EZW	Reducing Seal & Restraint Couplings	N	4"-12"		470 series w/ "B"	
EZW	Seal & Restraint Line Caps	N			Not available	
EZW	Flanged Coupling Adapters	N	4"-12"		911 or 920 w/ "B"	
471	Pipe-Lock Straight Restraint Sleeve Couplings (DI)	Y	4"-30"	B		
472	Pipe-Lock Straight Restraint Sleeve Couplings (PVC/HDPE)	Y	4"-24"	B		

Model Number	Product Description	BABA Status	Sizes Available	Special Designator (if required)	BABA Alternate Model Number	COMMENTS
473	Pipe-Lock Straight Restraint Sleeve Couplings	Y	PVC end 4"-24" DI end 4"-30"	B		PVC end is applicable to HDPE
477	Pipe-Lock Straight Restraint Sleeve (sleeve only)	Y	4"-48"	D		
911	Flange-Lock Flanged Coupling Adapter (DI)	Y	4"-30"	B		
920	Flange-Lock Flanged Coupling Adapter (PVC/HDPE)	Y	4"-24"	B		
923	Flange-Lock Flanged Coupling Adapter (body only)	Y		D		
907	Restraint Plates	Y	All sizes	Not applicable		2" ≥ thick use standard part number