



Pipe-Lock™

Sleeve



477

IMPORTANT LINKS

Click appropriate words to go to:

- [Standard Limited Warranty](#)
- [Sales Terms & Conditions](#)
- [Freight Policy](#)
- [Returns Policy](#)
- [Corrosion & Product Selection Notice](#)

Description:

This is a fabricated Steel sleeve for use with MJ gaskets and restraints.

Application:

For connecting plain end D.I. and plain end PVC

Materials Specifications (subject to change):

SLEEVE: ASTM A283 Gr. C or Carbon Steel having a minimum yield strength of 30,000 PSI.

FINISH: Flexi-Coat® Fusion-Bonded Epoxy

NOM PIPE SIZE INCHES	CATALOG NUMBER	SLEEVE THK. X LGTH IN.		APPROX SHIP WT LBS.	PRESSURE
		A	B		
3	477-00030003-200D	0.25	7	8	350 PSI
4	477-00040004-200D	0.25	7	12	350 PSI
6	477-00060006-200D	0.25	7	16	350 PSI
6	477-00060006-300D	0.25	10	21	350 PSI
8	477-00080008-200D	0.25	7	21	350 PSI
8	477-00080008-300D	0.25	10	27	350 PSI
10	477-00100010-200D	0.25	7	25	350 PSI
10	477-00100010-300D	0.25	10	33	350 PSI
12	477-00120012-200D	0.25	7	29	350 PSI
12	477-00120012-300D	0.25	10	38	350 PSI
14	477-00140014-200D	0.25	7	34	350 PSI
14	477-00140014-300D	0.25	10	44	350 PSI
16	477-00160016-200D	0.25	7	38	350 PSI
16	477-00160016-300D	0.25	10	50	350 PSI
18	477-00180018-200D	0.25	7	42	250 PSI
18	477-00180018-300D	0.25	10	56	250 PSI
20	477-00200020-200D	0.25	7	47	250 PSI
20	477-00200020-300D	0.25	10	62	250 PSI
24	477-00240024-200D	0.25	7	55	250 PSI
24	477-00240024-300D	0.25	10	73	250 PSI
30	477-00300030-300D	0.25	10	90	250 PSI
36	477-00360036-300D	0.25	10	107	225 PSI
42	477-00420042-300D	0.25	16	184	160 PSI
48	477-00480048-300D	0.25	10	141	140 PSI

470 Series Reducing Restraint Couplings and Sleeves available. Please contact Smith-Blair for more information.