

# e-1532X Smart Pump

powered by hydrovar® X

## Example product code

The various versions of the e-1532X line are identified by a product code number. This number is also the catalog number for the pump. The meaning of each digit in the product code number is shown below. Note: Not all combinations are possible.

1532X	A	1	M	5	S	X	1
-------	---	---	---	---	---	---	---

### Seal material

- (1) = BUNA/C/SC
- (2) = EPR SIC/SIC

### Motor/Drive

- (X) = hydrovar X+(High Tier)

### Voltage

- (R) = 200-240V (S) = 380-460V (3-phase only)

### Pole-Hz-phase

- (4) = 4-60-3 (2000-4000RPM)\*
- (5) = 4-60-3 (1200-2000RPM)\*

\* The frequency (Hz) listed is the supply frequency.

### HP rating

- (J) = 3                      (R) = 10                      (P) = 25
- (K) = 5.5                    (M) = 15                      (Q) = 30
- (L) = 7.5                    (N) = 20

### Pump size

- (1) = AD                      (5) = BD                      (10) = GC
- (2) = AC                      (6) = EB
- (3) = A                        (7) = G
- (11) = BB                    (8) = E
- (4) = BC                      (9) = GB

### Discharge size

- (A) = 1.25"                  (E) = 3"
- (B) = 1.5"                    (F) = 4"
- (C) = 2"                        (G) = 5"
- (D) = 2.5"                    (H) = 6"

### Pump series

- (1510X) = e-1510 with hydrovar X/X+ technology
- (1531X) = e-1531 with hydrovar X/X+ technology
- (1532X) = e-1532\*\* with hydrovar X/X+ technology

\*\*No baseplate

### Xylem Product Cybersecurity:

Xylem values your system security and the availability of your critical services. For more information on Xylem cybersecurity practices or to contact the cybersecurity team please visit [xylem.com/security](http://xylem.com/security).

Learn more about  
Series e-1532X  
Smart Pumps

