

Capacities & Media

	Filter Area (ft ²)	Min Flow (gpm)	Max Flow (gpm)	Perlite (lb)
SP-27-48-487	255	191	535	30
SP-33-48-732	383	287	805	45
SP-41-48-1038	543	408	1,141	64
SP-49-48-1548	811	608	1,702	96
SP-55-48-2076	1,087	815	2,283	128

Connection Sizes



	Inlet/Outlet (in)	Drain (in)
SP-27-48-487	6	3
SP-33-48-732	8	3
SP-41-48-1038	8	4
SP-49-48-1548	10	4
SP-55-48-2076	12	4

Size & Weights

	Capacity (gal)	Shipping Wt. (lb)	Operating Wt. (lb)
SP-27-48-487	159	1,650	2,970
SP-33-48-732	250	1,800	3,880
SP-41-48-1038	441	2,350	6,020
SP-49-48-1548	615	3,320	8,440
SP-55-48-2076	841	3,850	10,850

Dimensions

	A (in)	B (in)	C (in)	D (in)
SP-27-48-487	33.1	97.5	83.5	28.1
SP-33-48-732	38.5	103.3	89.8	31.0
SP-41-48-1038	47.0	104.8	91.3	32.5
SP-49-48-1548	54.1	109.3	95.8	35.0
SP-55-48-2076	61.2	110.5	97.0	36.0



Notes


- Filter Area based on uncoated flextubes.
- All models NSF 50 Certified to 3.00 gpm/ft².
- Minimum and Maximum Flowrates based on Neptune Benson recommended filter rates 0.75 - 2.10 gpm/ft².
- 16" clearance above filter recommended for service access.
- Inlet and Outlet Sizes based on 10 ft/s maximum pipe velocity.

Xylem
334 Knight St Ste 3100
Warwick, RI 02886 USA

Tel +1 800.832.8002
Tel +1 401.821.2200
xylem.com

Capacities & Media

	Filter Area (ft ²)	Min Flow (gpm)	Max Flow (gpm)	Perlite (lb)
SP-27-48-487-R	255	191	535	30
SP-33-48-732-R	383	287	805	45
SP-41-48-1038-R	543	408	1,141	64
SP-49-48-1548-R	811	608	1,702	96
SP-55-48-2076-R	1,087	815	2,283	128



Connection Sizes


	Inlet/Outlet (in)	Drain (in)
SP-27-48-487-R	6	3
SP-33-48-732-R	8	3
SP-41-48-1038-R	8	4
SP-49-48-1548-R	10	4
SP-55-48-2076-R	12	4

Size & Weights

	Capacity (gal)	Shipping Wt. (lb)	Operating Wt. (lb)
SP-27-48-487-R	159	1,650	2,970
SP-33-48-732-R	250	1,800	3,880
SP-41-48-1038-R	441	2,350	6,020
SP-49-48-1548-R	615	3,320	8,440
SP-55-48-2076-R	841	3,850	10,850

Dimensions

	A (in)	B (in)	C (in)	D (in)
SP-27-48-487-R	33.6	84.8	4.8	15.6
SP-33-48-732-R	38.5	90.8	4.8	18.5
SP-41-48-1038-R	47.0	92.5	5.5	20.3
SP-49-48-1548-R	54.1	97.0	5.5	22.7
SP-55-48-2076-R	61.2	98.1	5.5	23.7



Notes


- Filter Area based on uncoated flextubes.
- All models NSF 50 Certified to 3.00 gpm/ft².
- Minimum and Maximum Flowrates based on Neptune Benson recommended filter rates 0.75 - 2.10 gpm/ft².
- 16" clearance above filter recommended for service access.
- Inlet and Outlet Sizes based on 10 ft/s maximum pipe velocity.

Xylem
334 Knight St Ste 3100
Warwick, RI 02886 USA

Tel +1 800.832.8002
Tel +1 401.821.2200
xylem.com

Capacities & Media

	Filter Area (ft ²)	Min Flow (gpm)	Max Flow (gpm)	Perlite (lb)
SP-29-36-200	79	59	165	9
SP-29-36-250	98	74	206	11
SP-29-36-300	118	88	247	13
SP-29-36-350	137	103	289	16
SP-29-36-400	157	118	330	18
SP-29-36-450	177	133	371	20
SP-29-36-500	196	147	412	22




Connection Sizes

	Inlet/Outlet (in)	Drain (in)
SP-29-36-200	6	3
SP-29-36-250	6	3
SP-29-36-300	6	3
SP-29-36-350	6	3
SP-29-36-400	6	3
SP-29-36-450	6	3
SP-29-36-500	6	3

Size & Weights

	Capacity (gal)	Shipping Wt. (lb)	Operating Wt. (lb)
SP-29-36-200	181	735	2,250
SP-29-36-250	181	750	2,265
SP-29-36-300	181	765	2,280
SP-29-36-350	181	780	2,295
SP-29-36-400	181	795	2,310
SP-29-36-450	181	810	2,325
SP-29-36-500	181	825	2,340




Notes

- Filter Area based on uncoated flex tubes.
- All models NSF 50 Certified to 3.00 gpm/ft².
- Minimum and Maximum Flowrates based on Neptune Benson recommended filter rates 0.75 - 2.10 gpm/ft².
- 16" clearance above filter recommended for service access.
- Inlet and Outlet Sizes based on 10 ft/s maximum pipe velocity.
- 10½" height to center of drain connection.

Xylem
334 Knight St Ste 3100
Warwick, RI 02886 USA

Tel +1 800.832.8002
Tel +1 401.821.2200
xylem.com

Capacities & Media	Filter Area (ft ²)	Min Flow (gpm)	Max Flow (gpm)	Perlite (lb)
SP-33-36-732	287	216	604	35
SP-39-36-948	372	279	782	44
SP-43-36-1182	464	348	975	56
SP-47-36-1440	565	424	1,188	69
SP-50-36-1698	667	500	1,400	81
SP-55-36-2076	815	611	1,712	98




Certified to
NSF/ANSI/CAN 50

Connection Sizes	Inlet/Outlet (in)	Drain (in)
SP-33-36-732	6	3
SP-39-36-948	8	4
SP-43-36-1182	8	4
SP-47-36-1440	8	4
SP-50-36-1698	10	4
SP-55-36-2076	10	4

Size & Weights	Capacity (gal)	Shipping Wt. (lb)	Operating Wt. (lb)
SP-33-36-732	230	1,955	3,900
SP-39-36-948	337	2,545	5,400
SP-43-36-1182	404	2,820	6,240
SP-47-36-1440	467	3,210	7,170
SP-50-36-1698	545	3,540	8,160
SP-55-36-2076	652	4,030	9,565

Dimensions	A (in)	B (in)	C (in)	D (in)
SP-33-36-732	38.4	79.5	5.2	15.8
SP-39-36-948	45.5	79.3	5.5	18.0
SP-43-36-1182	49.0	79.9	5.5	18.5
SP-47-36-1440	52.7	79.3	5.5	19.0
SP-50-36-1698	56.0	80.0	5.5	17.8
SP-55-36-2076	61.2	80.4	5.5	18.4



Notes

- Filter Area based on uncoated flex tubes.
- All models NSF 50 Certified to 3.00 gpm/ft².
- Minimum and Maximum Flowrates based on Neptune Benson recommended filter rates 0.75 - 2.10 gpm/ft².
- 16" clearance above filter recommended for service access.
- Inlet and Outlet Sizes based on 10 ft/s maximum pipe velocity.

Xylem
334 Knight St Ste 3100
Warwick, RI 02886 USA

Tel +1 800.832.8002
Tel +1 401.821.2200
xylem.com