

68X Line Stop Outlets for Tapping Sleeves
For Line Stopping & Plugging Size on Size

Nominal Size Pipe x Flg. Outlet Inches	O.D. Range Inches	Epoxy Coated, Carbon Steel, Carbon Plate, Alloy Bolts & Nuts		Epoxy Coated, Carbon Steel, Carbon Plate, 304 Stainless Steel Bolts & Nuts		Approx Weight lbs.
		Catalog Number	List Price 110	Catalog Number	List Price 212	
4 x 4	4.74-4.86	68X-04800400-110	**P.O.A.**	68X-04800400-212	**P.O.A.**	50
4 x 4	5.10-5.35	68X-05100400-110	**P.O.A.**	68X-05100400-212	**P.O.A.**	50
6 x 6	6.57-6.73	68X-06630600-110	**P.O.A.**	68X-06630600-212	**P.O.A.**	115
6 x 6	6.84-7.10	68X-06900600-110	**P.O.A.**	68X-06900600-212	**P.O.A.**	115
6 x 6	7.00-7.20	68X-07100600-110	**P.O.A.**	68X-07100600-212	**P.O.A.**	115
8 x 8	8.36-8.75	68X-08630800-110	**P.O.A.**	68X-08630800-212	**P.O.A.**	175
8 x 8	8.98-9.30	68X-09050800-110	**P.O.A.**	68X-09050800-212	**P.O.A.**	175
8 x 8	9.40-9.60	68X-09400800-110	**P.O.A.**	68X-09400800-212	**P.O.A.**	175
10 x 10	10.45-10.88	68X-10751000-110	**P.O.A.**	68X-10751000-212	**P.O.A.**	220
10 x 10	11.03-11.30	68X-11101000-110	**P.O.A.**	68X-11101000-212	**P.O.A.**	220
10 x 10	11.36-11.80	68X-11401000-110	**P.O.A.**	68X-11401000-212	**P.O.A.**	220
12 x 12	12.63-12.88	68X-12751200-110	**P.O.A.**	68X-12751200-212	**P.O.A.**	300
12 x 12	13.12-13.37	68X-13201200-110	**P.O.A.**	68X-13201200-212	**P.O.A.**	300
12 x 12	14.20-14.40	68X-14251200-110	**P.O.A.**	68X-14251200-212	**P.O.A.**	300

12”-24” Pin Style Line Stop available in 687 and 689 series.

Line Stop Model	Tapping
682	662
683	663
684	664
685	665
687	622
689	625

Non Returnable Specials