Boxed chemfeed system

Duplex



General description

Duplex chemical dosing box with wetted components suited for most corrosive chemicals and PVC Free to comply with red list, PVDF/Viton
Part number: W3T585537

Product description

Preassembled boxed duplex chemical feed system
1 inlet, 1 outlet, ½" PFA tubing
Wall-mounted HDPE enclosure, junction box with pump cables factory-wired including TURK connectors

Configuration:
Flow capacity: 0.008 to 8 gph
Flow pressure: 0 to 60 psi
Pumped liquid: Custom
Custom materials of construction:
Dosing head (PVDF), O-rings (teflon), check balls (ceramic), DICE (PVDF), O-rings (VITON)
Remote start/stop: Yes
Pressure sensor: Yes
Analog inputs: Yes
Analog outputs: No
Relay output: Yes
Pulse control: Yes
Graphical display: Yes
Field bus: None
System type: Duplex
Panel type: JBox
Mounting type: Wall
Tube material: PFA
Ball valve type: Standard

Parts list:
Frame HDPE
Pumps, W2T845438
DDA 30-4 FCM-PV/T/C-F-31U7U7BG
DICE valve (W2T931695)
Calibration column, 100mL GLASS/VITON (W2T401734)
Panel, 4X J-box 2 pump DDA/DDE W/TURK (W3T538535)
Cables, control input cable (W2T430046)
Cables, relay output cable (W2T530020)

Optional pump service kits (sold separately) W2T531225

xylem.com

All information presented herein is believed reliable and in accordance with accepted engineering practices. Xylem makes no warranties as to the completeness of this information. Users are responsible for evaluating individual product suitability for specific applications. Xylem assumes no liability whatsoever for any special, indirect or consequential damages arising from the sale, resale or misuse of its products. Subject to change without notice.

© 2026 Xylem Inc. or its affiliates. All other trademarks are those of their respective owners.
HPS-W3T585537-DS-0826