

# CCFG Legacy™ Fiberglass Sand Filters

| Filter Model Number | Tank Conn | Filter Area (SF) | Max Flow (GPM) | All dimensions are in inches | | | | | | Tank Shipping Weight (LBS) | Operating Weight (LBS) |
|---|---|---|---|---|---|---|---|---|---|---|---|
| | | | | A | B | C | D | E | F | | |
| 42CCFG-3 | 3 | 9.6 | 115 | 64 | 43 | 44 | 38 | 13 3/4 | 13 3/4 | 111 | 2170 |
| 48CCFG-3 | 3 | 11.8 | 142 | 70 | 49 | 57 3/4 | 47 1/4 | 14 1/8 | 21 5/8 | 189 | 3410 |


| Face Piping Dimensions | | | |
|---|---|---|---|
| Dimen-sions | Face Piping Size (inches) Dual Tank | | |
| | 3x3 | 4x3 | 6x3 |
| G | 7 | 8 | 13 |
| H | 7 | 8 | 13 |





Model 42CCFG include a 6”x9” access port.




Shown with manual face piping.




Model 48CCFG includes a 14”x18” access manway.

## MEDIA REQUIREMENTS

| All dimensions are in inches STANDARD MEDIA CHART | | | |
|---|---|---|---|
| Filter Model Number | Gravel (CF) | Filter Sand (CF) | Sand Depth |
| 42CCFG-3 | 3 | 13 | 16 |
| 48CCFG-3 | 3 | 16 | 17 |




NSF Certified to NSF/ANSI/CAN 50

ML-4/29/26