

# e-1510X Smart Pump

powered by hydrovar® X

## Example product code

The various versions of the e-1510X line are identified by a product code number. This number is also the catalog number for the pump. The meaning of each digit in the product code number is shown below. Note: Not all combinations are possible.

1510X	A	1	M	5	S	X	1
-------	---	---	---	---	---	---	---

### Seal material

- (1) = BUNA/C/SC
- (2) = EPR SIC/SIC

### Motor/Drive

- (X) = hydrovar X+(High Tier)

### Voltage

- (R) = 200-240V (S) = 380-460V (3-phase only)

### Pole-Hz-phase

- (4) = 4-60-3 (2000-4000RPM)\*
- (5) = 4-60-3 (1200-2000RPM)\*

\* The frequency (Hz) listed is the supply frequency.

### HP rating

- (J) = 3 (R) = 10 (P) = 25
- (K) = 5.5 (M) = 15 (Q) = 30
- (L) = 7.5 (N) = 20

### Pump size

- (1) = AD (5) = BD (10) = GC
- (2) = AC (6) = EB
- (3) = A (7) = G
- (11) = BB (8) = E
- (4) = BC (9) = GB

### Discharge size

- (A) = 1.25" (E) = 3"
- (B) = 1.5" (F) = 4"
- (C) = 2" (G) = 5"
- (D) = 2.5" (H) = 6"

### Pump series

- (1510X) = e-1510 with hydrovar X/X+ technology
- (1531X) = e-1531 with hydrovar X/X+ technology
- (1532X) = e-1532\*\* with hydrovar X/X+ technology

\*\*No baseplate

### Xylem Product Cybersecurity:

Xylem values your system security and the availability of your critical services. For more information on Xylem cybersecurity practices or to contact the cybersecurity team please visit [xylem.com/security](http://xylem.com/security).

Learn more about  
Series e-1510X  
Smart Pumps



### Xylem

[xylem.com/bellgossett](http://xylem.com/bellgossett)

This information is subject to change without notice. All information presented herein is believed reliable and in accordance with accepted engineering practices. Xylem makes no warranties as to the completeness of this information. Users are responsible for evaluating individual product suitability for specific applications. Xylem assumes no liability whatsoever for any special, indirect or consequential damages arising from the sale, resale or misuse of its products.

© 2026 Xylem Inc. or its affiliate. All rights reserved. Xylem, Bell & Gossett and Hydrovar are registered trademarks of Xylem Inc. or one of its subsidiaries. All other trademarks or registered trademarks are the property of their respective owners.