


Job:

Order number: _____
Submitted by: _____
Approved by: _____

Representative:

Unit tag: _____
Engineer: _____
Contractor: _____

Date: _____
Date: _____
Date: _____



MODEL MV

Venturi Ball/Valve Combination

Description

Bell & Gossett's Model MV is a combination calibrated balance, commissioning and positive shut-off valve for use in HVAC systems. An efficient brass Venturi design provides accurate flow balancing with minimal system pressure loss. Valves are furnished with two pressure / temperature ports, standard port ball valve with memory stop, and a hanging ID tag for commissioning. A variety of end connections are available on both the fixed and union ends.

Maximum working pressure

400 psig (2,758 kPa)

Maximum operating temperature

40°F (5°C) to 250°F (121°C)

Construction

- Venturi body: Cast brass ASTM B763-08A
- Ball valve: Forged brass ASTM B283-06
- O-ring: EPDM
- PT seal: EPDM Dual Durometer Core
- Handle: chrome plated steel
- Memory stop: 302 Stainless Steel
- Stem: Brass ASTM B124-09, Blow Out Proof
- Ball: Chrome plated brass
- Ball seat: Teflon
- Packing nut: Brass ASTM B124-09
- Packing gland: Teflon


Accuracy

- +/- 1% Between 10" W.C. & 70" W.C.
- +/- 3% Between 5" W.C. & 150" W.C.
- +/- 5% Less than 5" W.C. & Over 150" W.C.

Schedule

Valve size/fixed end	Tagging information	Quantity
½" L sweat female		
½" L NPT female		
½" H sweat female		
½" H NPT female		
¾" UL sweat female		
¾" UL NPT female		
¾" L sweat female		
¾" L NPT female		
¾" H sweat female		
¾" H NPT female		
1" sweat female		
1" NPT female		
1¼" sweat female		
1¼" NPT female		
1½" sweat female		
1½" NPT female		
2" sweat female		
2" NPT female		

Model MV



Valve size/fixed end	Recommended flow rate GPM (L/M)	CV	Dimensions* in inches (mm)				Approx. Wt. Lbs. (Kg)
			A	B	P	W	
½"L sweat female	0.3 - 1.8 (1.14 - 6.8)	0.55	4.8 (122)	5.5 (140)	2.1 (53)	1.6 (40.6)	1.23 (0.6)
½"L NPT female	0.3 - 1.8 (1.14 - 6.8)	0.55	4.5 (114)	5.1 (130)	2.1 (53)	1.6 (40.6)	1.23 (0.6)
½"H sweat female	0.8 - 4.2 (3.0 - 15.8)	1.6	4.8 (122)	5.5 (140)	2.1 (53)	1.6 (40.6)	1.23 (0.6)
½"H NPT female	0.8 - 4.2 (3.0 - 15.8)	1.6	4.5 (114)	5.1 (130)	2.1 (53)	1.6 (40.6)	1.23 (0.6)
¾"UL sweat female	0.3 - 1.8 (1.14 - 6.8)	0.55	5.2 (132)	6.0 (152)	2.1 (53)	1.6 (40.6)	1.50 (0.7)
¾"UL NPT female	0.3 - 1.8 (1.14 - 6.8)	0.55	4.7 (119)	5.5 (139)	2.1 (53)	1.6 (40.6)	1.50 (0.7)
¾"L sweat female	0.8 - 4.2 (3.0 - 15.8)	1.6	5.2 (132)	6.0 (152)	2.1 (53)	1.8 (46)	1.50 (0.7)
¾"L NPT female	0.8 - 4.2 (3.0 - 15.8)	1.6	4.7 (119)	5.5 (139)	2.1 (53)	1.8 (46)	1.50 (0.7)
¾"H sweat female	1.8 - 8.9 (6.8 - 33.7)	3.1	5.2 (132)	6.0 (152)	2.1 (53)	1.8 (46)	1.50 (0.7)
¾"H NPT female	1.8 - 8.9 (6.8 - 33.7)	3.1	4.7 (119)	5.5 (139)	2.1 (53)	1.8 (46)	1.50 (0.7)
1" sweat female	2.8 - 15.0 (10.61 - 56.82)	5	5.7 (148)	6.7 (170)	2.2 (56)	2.1 (53)	2.45 (1.11)
1" NPT female	2.8 - 15.0 (10.61 - 56.82)	5	5.1 (129)	6.0 (152)	2.2 (56)	2.1 (53)	2.45 (1.11)
1¼" sweat female	4.8 - 24.0 (18.2 - 90.8)	8.8	6.5 (165)	7.5 (190)	2.4 (61)	2.8 (71)	3.50 (1.59)
1¼" NPT female	4.8 - 24.0 (18.2 - 90.8)	8.8	5.8 (52)	6.7 (168)	2.4 (61)	2.8 (71)	3.50 (1.59)
1½" sweat female	7.5 - 35.5 (28.4 - 134.4)	13	8.0 (203)	9.1 (231)	2.7 (68)	3.1 (79)	4.81 (2.18)
1½" NPT female	7.5 - 35.5 (28.4 - 134.4)	13	7.0 (179)	8.2 (208)	2.7 (68)	3.1 (79)	4.81 (2.18)
2" sweat female	12.0 - 69.3 (45.4 - 262.3)	24	8.7 (221)	9.8 (249)	3.0 (76)	3.8 (96)	7.25 (3.29)
2" NPT female	12.0 - 69.3 (45.4 - 262.3)	24	7.6 (193)	8.7 (221)	3.0 (76)	3.8 (96)	7.25 (3.29)

*All dimensions +/- 0.125" tolerance. Dimensions are subject to change. Not to be used for construction purposes unless certified. Please see Data Chart #EP-600

Xylem inc. xylem.com/bellgossett

This information is subject to change without notice. All information presented herein is believed reliable and in accordance with accepted engineering practices. Xylem makes no warranties as to the completeness of this information. Users are responsible for evaluating individual product suitability for specific applications. Xylem assumes no liability whatsoever for any special, indirect or consequential damages arising from the sale, resale or misuse of its products.

© 2026 Xylem Inc. or its affiliate. All rights reserved. Xylem, Bell & Gossett and Circuit Sentry are registered trademarks of Xylem Inc. or one of its subsidiaries. All other trademarks or registered trademarks are the property of their respective owners.

A-606.40E 3/2026

xylem
Let's Solve Water