



Pipe-Lock™

470 Series Components Chart

Gasket

NOMINAL PIPE SIZE INCHES	DUCTILE IRON		IPS		MULTI-SEAL	
	OD	CATALOG NUMBER	OD	CATALOG NUMBER	OD	CATALOG NUMBER
3	3.96	000-00038572-060	3.50	000-00038573-060	-	-
4	4.80	000-00036142-060	4.50	000-00038517-060	4.50-4.80	000-00036735-060
6	6.90	000-00036143-060	6.63	000-00038518-060	6.63-6.90	000-00036736-060
8	9.05	000-00036144-060	8.63	000-00038519-060	8.63-9.05	000-00036737-060
10	11.10	000-00036145-060	10.75	000-00038520-060	10.75-12.75	000-00036738-060
12	13.20	000-00036146-060	12.75	000-00038521-060	12.75-13.20	000-00036739-060
14	15.30	000-00038496-060				
16	17.40	000-00038497-060				
18	19.50	000-00038498-060				
20	21.60	000-00038499-060				
24	25.80	000-00038500-060				

Studs for 7" Sleeve

NOMINAL PIPE SIZE INCHES	STUD CATALOG NUMBER	DESCRIPTION	NUT CATALOG NUMBER	DESCRIPTION
3	000-00090225-005	5/8" x 16" All-Thread Alloy	000-000100025-005	5/8" Hex Head Alloy
4-24	101-00090241-005	3/4" x 18" All-Thread Alloy Set Includes 1 Stud & 2 Nuts		

Studs for 10" Sleeve


NOMINAL PIPE SIZE INCHES	STUD SET CATALOG NUMBER	DESCRIPTION
6-24	101-00090218-005	3/4" x 20" All-Thread Alloy. Set Includes 1 Stud & 2 Nuts.
30-36	101-00090840-005	1" x 24" All-Thread Alloy. Set includes 1 Stud & 2 Nuts.
42-48	101-00090842-005	1 1/4" x 24" All-Thread Alloy. Set includes 1 Stud & 2 Nuts.

Number of Studs Required

NOMINAL PIPE SIZE INCHES	STUD QUANTITY
3	4
4	4
6	6
8	6
10	8
12	8
14	10
16	12
18	12
20	14
24	16
30	20
36	24
42	28
48	32

Studs for 16" Sleeve

NOMINAL PIPE SIZE INCHES	STUD SET CATALOG NUMBER	DESCRIPTION
30-36	101-00090841-005	1" x 30" All-Thread Alloy. Set includes 1 Stud & 2 Nuts.
42-48	101-00090843-005	1 1/4" x 30" All-Thread Alloy. Set includes 1 Stud & 2 Nuts.



Pipe-Lock™

Fabricated Steel Restraint Couplings

FOR PVC PIPE Patents US 7484775, US 7745100, CA 2511782

472

IMPORTANT LINKS

Click appropriate words to go to:

[Standard Limited Warranty](#)
[Sales Terms & Conditions](#)
[Freight Policy](#)
[Returns Policy](#)
[Corrosion & Product Selection Notice](#)



Description: This is a fabricated Steel restraint coupling.

Application: Joins and restrains from PVC pipe to PVC pipe with no other method of restraining pipe required.

Key Features:

- Mechanical restraint shall be an integral part of the follower gland utilizing multiple single tooth wedges
- Comes as a complete unit (sleeve, 2 Cam-Locks, 2 gaskets, appropriate number of studs) or as a sleeve only to use with your existing inventory
- Use with the Multi-Seal Gasket for more flexibility in nominal sizes 4"-12" — mixing IPS and D.I. O.D. PVC
- Breakaway nut torque per wedge is 45 to 60 ft. lbs
- Coupling is rated at the working pressure shown on page 30
- Longer sleeves available

Materials Specifications (subject to change):

SLEEVE: ASTM A283 Gr. C or Carbon Steel having a minimum yield of 30,000 PSI

FINISH: Flexi-Coat® Fusion-Bonded Epoxy

Cam-Lock™ Specifications:

GLAND: 65-45-12 Ductile Iron (ASTM A536)

WEDGES: Single Tooth, Ductile Iron, heat treated for Ductile Iron pipe applications

ACTUATING BOLTS: 60-40-18 Ductile Iron (ASTM A536)

BREAKAWAY NUTS: Carbon Steel or Cast Iron

FINISH: Gland is Flexi-Coat® Fusion-Bonded Epoxy, per AWWA C213; Wedges and actuating bolts are E-coated Epoxy

Kit Specifications:

GASKET: SBR Standard Mechanical Joint. Per ANSI/AWWA C111/A21.11 SBR, Multi-Seal Gasket, or MJ transition gasket for Steel/IPS ODs. *Optional multi-seal gasket available in 4"-12" sizes; 30" and 36" sizes supplied with Smith-Blair® MJ gasket.*

STUDS/NUTS: High strength, low alloy, per AWWA C111; *Optional: 304 Stainless Steel fluoropolymer-coated nuts.*

Pipe Applications: PVC

Sizes (in inches): 3, 4, 6, 8, 10, 12, 14, 16, 18, 20, 24, 30, 36

Working Pressure: See Pressure Chart on next page.

Deflection: Assembled joints into each follower gland through 12" shall allow for three degree deflection on 3", five degrees on 4"-12", two degrees 14"-24", 1.5 degrees 18"-24", one degree 30"-48".



Pipe-Lock™

Fabricated Steel Restraint Couplings

FOR PVC PIPE Patents US 7484775, US 7745100, CA 2511782

472

Pipe Type and Pressure Rating (PSI)

NOM. SIZE	PVC	DUCTILE IRON	STEEL	
3"	Rated at the pressure rating of the PVC pipe on which it is installed. See PVC pressure rating chart.	350	250	
4"		350	250	
6"		350	250	
8"		350	250	
10"		350	250	
12"		350	250	
14"		350	-	
16"		350	-	
20"		250	-	
24"		250	-	
30"		150	250	-
36"		125	250	-
42"	-	250	-	
48"	-	250	-	

Pressure Ratings (PSI) for Cam-Locks™ on PVC Pipe

ANSI/AWWA C900 D.I. OD		ANSI/AWWA C905 D.I. OD		ASTM D2241 IPS / STEEL OD	
DR 14	305	DR 18	235	SDR 17	250
DR 18	235	DR 25	165*	SDR 21	200
DR 25	165			SDR 26	160

*ANSI/AWWA C905 DI OD- 30":150 PSI. 36":125 PSI.

The pressure rating for a Pipe-Lock will be the smaller of the two pipes when coupling/restraining together pipes with different pressure ratings.

Examples:

- If joining 24" DI to 24" DR18 C905 PVC, the working pressure would be 235 PSI.
- If joining 8" DI to 8" Steel, the working pressure would be 250 PSI.
- If joining 36" DR25 C905 PVC to 48" DI, the working pressure would be 125 PSI.
- If joining 10" Steel to 10" SDR21 PVC pipe, the working pressure would be 200 PSI.

Straight – PVC x PVC

NOMINAL PIPE SIZE INCHES	PIPE O.D. INCHES	CATALOG NUMBER	SLEEVE THK. X LGTH. IN.		STUDS			APPROX. SHIP WT. LBS.
			(A)	(B)	NO.	DIA. IN.	LGTH. IN.	
3	3.50	472-00000350-203	0.25	7	4	0.63	16	29
*4	*4.50-4.80 x *4.50-4.80	472-00000480-243	0.25	7	4	0.75	18	36
4	4.50	472-00000450-203	0.25	7	4	0.75	18	36
4	4.80	472-00000480-203	0.25	7	4	0.75	18	36
*6	*6.63-6.90 x *6.63 x 6.90	472-00000690-243	0.25	7	4	0.75	18	52
*6	*6.63-6.90 x *6.63 x 6.90	472-00000690-343	0.25	10	6	0.75	20	61
6	6.63	472-00000663-203	0.25	7	6	0.75	18	52
6	6.63	472-00000663-303	0.25	10	6	0.75	20	61
6	6.90	472-00000690-203	0.25	7	6	0.75	18	52
6	6.90	472-00000690-303	0.25	10	6	0.75	20	61
*8	*8.63-9.05 x *8.63-9.05	472-00000905-243	0.25	7	6	0.75	18	62
*8	*8.63-9.05 x *8.63-9.05	472-00000905-343	0.25	10	6	0.75	20	71
8	8.63	472-00000863-203	0.25	7	6	0.75	18	62
8	8.63	472-00000863-303	0.25	10	6	0.75	20	71
8	9.05	472-00000905-203	0.25	7	6	0.75	18	62

A= Sleeve Thickness B=Sleeve Length

*Uses Mult-Seal Gasket

Straight – PVC x PVC Continued

NOMINAL PIPE SIZE INCHES	PIPE O.D. INCHES	CATALOG NUMBER	SLEEVE THK. X LGTH. IN.		STUDS			APPROX. SHIP WT. LBS.
			(A)	(B)	NO.	DIA. IN.	LGTH. IN.	
8	9.05	472-00000905-303	0.25	10	6	0.75	20	71
*10	*10.75-11.10 x *10.75-11.10	472-00001110-243	0.25	7	8	0.75	18	92
*10	*10.75-11.10 x *10.75-11.10	472-00001110-343	0.25	10	8	0.75	20	103
10	10.75	472-00001075-203	0.25	7	8	0.75	18	92
10	10.75	472-00001075-303	0.25	10	8	0.75	20	103
10	11.10	472-00001110-203	0.25	7	8	0.75	18	92
10	11.10	472-00001110-303	0.25	10	8	0.75	20	103
*12	*12.75-13.20 x *12.75-13.20	472-00001320-243	0.25	7	8	0.75	18	114
*12	*12.75-13.20 x *12.75-13.20	472-00001320-343	0.25	10	8	0.75	20	125
12	12.75	472-00001275-203	0.25	7	8	0.75	18	114
12	12.75	472-00001275-303	0.25	10	8	0.75	20	125
12	13.20	472-00001320-203	0.25	7	8	0.75	18	114
12	13.20	472-00001320-303	0.25	10	8	0.75	20	125
14	15.30	472-00001530-203	0.25	7	10	0.75	18	142
14	15.30	472-00001530-303	0.25	10	10	0.75	20	157
16	17.40	472-00001740-203	0.25	7	12	0.75	18	172
16	17.40	472-00001740-303	0.25	10	12	0.75	20	190
18	19.50	472-00001950-203	0.25	7	12	0.75	18	190
18	19.50	472-00001950-303	0.25	10	12	0.75	20	208
20	21.60	472-00002160-203	0.25	7	14	0.75	18	218
20	21.60	472-00002160-303	0.25	10	14	0.75	20	240
24	25.80	472-00002580-203	0.25	7	16	0.75	18	272
24	25.80	472-00002580-303	0.25	10	16	0.75	20	297
30+	32.00	472-00003200-303	0.25	10	20	1.00	24	650
30+	32.00	472-00003200-503	0.25	16	20	1.00	30	793
36+	38.30	472-00003830-203	0.25	10	24	1.00	24	821
36+	38.30	472-00003830-503	0.25	16	24	1.00	30	993

A= Sleeve Thickness B=Sleeve Length

*Uses Multi-Seal Gasket

+ Uses Smith-Blair MJ Gasket