


13AI/BF (4 pole) Performance Comparison

1750 RPM – 4 pole



Previous impeller	Previous impeller dia. (in)	Current impeller	Current impeller dia. (in)
A	13.06	A	13.06
B	12.75	B	12.75
C	11.88	C	12.25
D	11.38	D	11.75
E	9.88	E	11.25
F	9.38	F	10.75
-	-	G	10.25
-	-	H	9.50

Xylem Inc.

www.xylem.com/goulds

This information is subject to change without notice. All information presented herein is believed reliable and in accordance with accepted engineering practices. Xylem makes no warranties as to the completeness of this information. Users are responsible for evaluating individual product suitability for specific applications. **Xylem assumes no liability whatsoever for any special, indirect or consequential damages arising from the sale, resale or misuse of its products.**

© 2026 Xylem Inc. or its affiliate. Xylem is a registered trademark of Xylem Inc. or one of its subsidiaries. Goulds is a registered trademark of ITT Manufacturing Enterprises LLC and is used under license. All other trademarks or registered trademarks are the property of their respective owners.