



xylem

Wastewater Portfolio

Solving wastewater for applications
requiring up to 40 HP

Complete. Reliable. Blue.

Xylem’s Gould’s Water Technology product line delivers a complete portfolio of wastewater pumps with a wide range of horsepower.

All are built to perform and last. All are backed by over 170 years of experience. And all are clad in our traditional Goulds Water Technology shade of blue. You’ll know it’s a quality wastewater pump when it’s a blue wastewater pump.

- Unprecedented durability
- Superior seal strength
- Thoroughly proven to devour solids and fibers, and resist clogging
- Sold through professional independent dealers
- Eligible for Goulds Professional Dealers Association (GPDA) member rewards

Superior seal strength

The most vulnerable part in a pump is the mechanical seal. For many models, both the the stationary and rotary faces of our seals are constructed of sintered, chemical grade silicon carbide. This is the toughest, most reliable mechanical seal face combination, ideal for the demanding wastewater environment, and available on many of our pumps.

	Carbon ceramic	Silicone carbide	Performance ratio
Hardness	600	2,700	4.5
Tensile strength	6,000 PSI	45,000 PSI	7.5
Compression strength	22,000 PSI	360,000 PSI	16.4
Temperature	525°F	3,000°F	5.7

Impeller design

Impellers are an essential component of any wastewater pump required to handle solids. Goulds Water Technology wastewater pump portfolio includes of a variety of impeller technologies designed to tackle your specific application.

- Non-clog channel/vane: Typically a two-vane design.
- Vortex: Recessed into the pump casing, this design allows the solids to pass without touching the vanes.
- Rotary cutter + impeller: This design incorporates a two-blade cutter with an internal cutter ring.
- Axial grinder + impeller: The Xylem axial grinder is designed with a three blade cutter and an eight-hole cutter plate paired with a semi-open impeller.


Non-clog channel/vane



Vortex



Rotary grinder



Axial grinder



Wastewater portfolio

	Models (Bolded represents premium seal standard)	Materials of construction	Performance range	HP range	Phase	Discharge sizes
Sump	GSP, LSP, 1DW, 2DW	- Cast iron - Engineered composites - Stainless steel	Up to 110 gpm, 66' TDH	1/3 – 1 1/2	1Ø-3Ø	1 1/4" – 1 1/2" NPT and 2" hose
Effluent	20AE, EB, PE, EP, WE, 2ED		Up to 142 gpm, 240' TDH	1/3 – 2		1 1/4" – 1 1/2" and 2" NPT
Sewage (Non-clog)	PS, 2WD, WS_B, WS_BF, WS_BHF, WS_D3, WS_D4, 3SD, 4SD, 3SDX, 4SDX, 4NS		Up to 1,200 gpm, 140' TDH	1/3 – 40		2" and 3" NPT, 3" and 4" flanged
Sewage (vortex)	PV, WW, VTX					
Grinders	AGS, RGS, 1GD, 1GA, 2GA	- Cast iron - Silicon bronze - Hardened steel	Up to 200 gpm, 180' TDH	1/2 - 11		1 1/4" – 1 1/2" and 2" NPT



Pump / basin packages

Available models: sump, effluent, sewage, and grinder

Materials of construction:

- Fiberglass basin can be engineered and assembled for delivery to your site
- Ribbed polyethylene basins with structural foam or steel covers assembled and in stock
- Roll top polyethylene basins with structural foam cover assembled and in stock

Features and benefits:

- Supplied completely assembled or installer can install piping to fit installation needs
- Systems available with 1 1/4" – 4" piping

Grinder packages

Features and benefits:

- Simplex and duplex basin assemblies in 1.25" and 2" discharge
- Solid basin covers. Vent must be field installed per local code
- Basins are not pre-drilled for electrical or inlet grommet holes and should be field installed. Parts are shipped loose
- Guide rail or non-guide rail equipped options.

Wastewater package system

Features and benefits:

- Completely assembled basin kit for 2" connection
- Simplex and duplex configurations available
- Conery base elbow disconnects 2"
- Easy pump installation
- Valves and piping complete
- True union isolation valve
- Stainless steel guide rails
- Installed stainless steel float bracket
- Inlet hub shipped loose



Control panels


- Stock controls feature the most popular options
- Available in simplex and duplex designs
- Controllers can be custom designed to your specifications
- Many panel styles in stock for immediate delivery

Float switches

- Pump and control type
- Direct connection for up to 20 amps

Piping and accessories

- Check valves
- Guide rail systems
- Pipe fittings
- Junction boxes



Additional resources

Training and education: Goulds Water Technology offers a variety of training resources available to support wastewater professionals.

- Hands-on factory schools
- e-Learning courses
- Webinars
- Podcasts
- On-demand videos




Selection software: Xylem Solver is a pump solution software with multiple search options and helpful project management facilities.

Xylem Solver allows any user to search by application, or product type without having detailed knowledge of Xylem products. The Solver platform also has the ability to guide the user to the right product for their particular needs.

Learn more: To learn more about the benefits of partnering with Goulds Water Technology as the single source for your complete wastewater needs, visit Goulds.com/CompleteWastewater or scan the QR code on this page.

**COMPLETE.
RELIABLE. BLUE.**
Learn more about
our complete line
of wastewater
products.



Xylem Inc. xylem.com/goulds

This information is subject to change without notice. All information presented herein is believed reliable and in accordance with accepted engineering practices. Xylem makes no warranties as to the completeness of this information. Users are responsible for evaluating individual product suitability for specific applications. Xylem assumes no liability whatsoever for any special, indirect or consequential damages arising from the sale, resale or misuse of its products.

© 2026 Xylem Inc. or its affiliate. All rights reserved. Xylem is a trademark of Xylem, Inc., or one of its subsidiaries. Goulds Water Technology is a registered trademark of ITT Manufacturing Enterprises LLC and is used under license. MODBUS is a registered trademark of Schneider Electric USA, Inc. All other trademarks or registered trademarks are the property of their respective owners.