




## Series e-80X/e-80SCX Smart Pump

Integrated pump, motor & variable speed drive solutions, powered by hydrovar® X

### e-80X/e-80SCX product line

This listing details replacement part information for the hydrovar X integrated motor-drive for the e-80X and e-80SCX product line. For pump-end replacement part information, see the standard e-80 Parts List CP-114-PL.



**Table 1: Available replacement kits**

| Item | Part name                              |
|------|--|
| 1    | hydrovar X motor and drive replacement |
| 2    | hydrovar X drive-only replacement kit  |
| 3    | hydrovar X motor-only replacement kit  |

**Table 2: Replacement kits for e-80X (JM Frame Motors)**

| hydrovar X Information |            |           |     |           |         | Replacement kit part number |                     |                     |
|------------------------|------------|-----------|-----|-----------|---------|-----------------------------|---------------------|---------------------|
| Motor type             | Motor code | Frame     | HP  | Speed     | Voltage | Motor+drive (item 1)        | Drive only (item 2) | Motor only (item 3) |
| EXM143-145JM/3.030BH4  | 130635811  | 143-145JM | 3   | Low       | 200-240 | 100635811                   | KL55ANA             | KL60AH0             |
| EXM143-145JM/4.030BH4  | 130635810  |           | 3   | Low       | 380-480 | 100635810                   |                     | KL60AHZ             |
| EXM143-145JM/4.075BH2  | 130635410  |           | 7.5 | High      |         | 100635410                   |                     | KL60AF0             |
| EXM213-215JM/3.055CH4  | 130636611  | 213-215JM | 5.5 | Low       | 200-240 | 100636611                   | KL55ANC             | KL60AGL             |
| EXM213-215JM/3.075CH4  | 130636731  |           | 7.5 |           |         | 100636731                   |                     | KL60AGN             |
| EXM213-215JM/3.075CH2  | 130637691  |           | 7.5 |           |         | High                        |                     | 100637691           |
| EXM213-215JM/4.055CH4  | 130636610  |           | 5.5 | Low       | 380-480 | 100636610                   |                     | KL60AGM             |
| EXM213-215JM/4.075CH4  | 130636730  |           | 7.5 |           |         | 100636730                   |                     | KL60AGP             |
| EXM213-215JM/4.100CH2  | 130636250  |           | 10  |           |         | High                        |                     | 100636250           |
| EXM213-215JM/4.150CH2  | 130636370  |           | 15  | 100636370 |         |                             |                     | KL60AGN             |

(continued on next page)

**Table 2: Replacement kits for e-80X (JM Frame Motors) (continued)**

| hydrovar X information |            |           |    |       |           | Replacement kit part number |                     |                     |
|------------------------|------------|-----------|----|-------|-----------|-----------------------------|---------------------|---------------------|
| Motor type             | Motor code | Frame     | HP | Speed | Voltage   | Motor+drive (item 1)        | Drive only (item 2) | Motor only (item 3) |
| EXM254-256JM/3.100DH4  | 130637451  | 254-256JM | 10 | Low   | 200-240   | 100637451                   | KL55ANE             | KL60AKX             |
| EXM254-256JM/3.150DH4  | 130637571  |           | 15 |       |           | 100637571                   |                     | KL60AHE             |
| EXM254-256JM/3.150DH2  | 130637771  |           | 15 | High  |           | 100637771                   |                     | KL60AG7             |
| EXM254-256JM/3.200DH2  | 130636971  |           | 20 |       |           | 100636971                   |                     | KL60AHB             |
| EXM254-256JM/4.100DH4  | 130637450  |           | 10 | Low   | 380-480   | 100637450                   |                     | KL60AHC             |
| EXM254-256JM/4.150DH4  | 130637570  |           | 15 |       |           | 100637570                   |                     | KL60AHF             |
| EXM254-256JM/4.200DH2  | 130636970  |           | 20 | High  |           | 100636970                   |                     | KL60AG9             |
| EXM254-256JM/4.250DH2  | 130637090  |           | 25 |       |           | 100637090                   |                     | KL60AHD             |
| EXM254-256JM/4.300DH2  | 130637210  |           | 30 |       | 100637210 | KL60AHE                     |                     |                     |

**Table 3: Replacement kits for e-80SCX (TC Frame Motors)**

| hydrovar X information |            |           |           |           |           | Replacement kit part number |                     |                     |         |         |
|------------------------|------------|-----------|-----------|-----------|-----------|-----------------------------|---------------------|---------------------|---------|---------|
| Motor type             | Motor code | Frame     | HP        | Speed     | Voltage   | Motor+drive (item 1)        | Drive only (item 2) | Motor only (item 3) |         |         |
| EXM143-145TC/3.030BH4  | 130635771  | 143-145TC | 3         | Low       | 200-240   | 100635771                   | KL55ANA             | KL60AH1             |         |         |
| EXM143-145TC/4.030BH4  | 130635770  |           | 3         | Low       | 380-480   | 100635770                   |                     | KL60AFS             |         |         |
| EXM143-145TC/4.075BH2  | 130635370  |           | 7.5       | High      |           | 100635370                   |                     | KL60AFR             |         |         |
| EXM213-215TC/3.055CH4  | 130636571  | 213-215TC | 5.5       | Low       | 200-240   | 100636571                   | KL55ANC             | KL60AKF             |         |         |
| EXM213-215TC/3.075CH4  | 130636691  |           | 7.5       |           |           | 100636691                   |                     | KL60AKP             |         |         |
| EXM213-215TC/3.075CH2  | 130636091  |           | 7.5       | High      |           | 100636091                   |                     | KL60AGA             |         |         |
| EXM213-215TC/4.055CH4  | 130636570  |           | 5.5       | Low       |           | 380-480                     |                     | 100636570           | KL60AGD |         |
| EXM213-215TC/4.075CH4  | 130636690  |           | 7.5       |           | 100636690 |                             |                     | KL60AGF             |         |         |
| EXM213-215TC/4.100CH2  | 130636210  |           | 10        | High      | 100636210 |                             |                     | KL60AKR             |         |         |
| EXM213-215TC/4.150CH2  | 130636330  |           | 15        |           | 100636330 |                             |                     | KL60AKT             |         |         |
| EXM254-256TC/3.100DH4  | 130637411  |           | 254-256TC | 10        | Low       | 200-240                     |                     | 100637411           | KL55ANE | KL60AKY |
| EXM254-256TC/3.150DH4  | 130637531  |           |           | 15        |           |                             |                     | 100637531           |         | KL60AK1 |
| EXM254-256TC/3.150DH2  | 130636811  |           |           | 15        | High      |                             |                     | 100636811           |         | KL60AGZ |
| EXM254-256TC/3.200DH2  | 130636931  | 20        |           | 100636931 |           |                             | KL60AG1             |                     |         |         |
| EXM254-256TC/4.100DH4  | 130637410  | 10        |           | Low       | 380-480   | 100637410                   | KL60AHQ             |                     |         |         |
| EXM254-256TC/4.150DH4  | 130637530  | 15        |           |           |           | 100637530                   | KL60AG4             |                     |         |         |
| EXM254-256TC/4.200DH2  | 130636930  | 20        |           | High      |           | 100636930                   | KL60AG0             |                     |         |         |
| EXM254-256TC/4.250DH2  | 130637050  | 25        |           |           |           | 100637050                   | KL60AG2             |                     |         |         |
| EXM254-256TC/4.300DH2  | 130637170  | 30        |           |           | 100637170 | KL60AK4                     |                     |                     |         |         |



Learn more about  
e-80X/e-80SCX Smart Pumps

**Xylem Product Cybersecurity:**

Xylem values your system security and the availability of your critical services. For more information on Xylem cybersecurity practices or to contact the cybersecurity team please visit [xylem.com/security](http://xylem.com/security).

Xylem Inc.

[www.xylem.com/bellgossett](http://www.xylem.com/bellgossett)

Subject to change without notice. All information presented herein is believed reliable and in accordance with accepted engineering practices. Xylem makes no warranties as to the completeness of this information. Users are responsible for evaluating individual product suitability for specific applications. Xylem assumes no liability whatsoever for any special, indirect or consequential damages arising from the sale, resale or misuse of its products.

© 2025 Xylem, Bell & Gossett and Hydrovar are registered trademarks of Xylem Inc. or one of its subsidiaries. MODBUS is a registered trademark of Schneider Electric USA, Inc. The Bluetooth word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Xylem Inc. or one of its subsidiaries is under license. All other trademarks or registered trademarks are the property of their respective owners.

